

Rugged Remote



Rugged Remote | Specifications

• Display	4 lines Liquid Cristal Display	
	fully backlit	
• Keypad	27 keys fully backlit	
	5 programmable function keys	
• Connections	XLR port	2 way hardwired remote port
		lamp info module port
	RS 232/422 port	
• Communication (baud)	switch RS 422T - RS 422NT - RS232	
	XLR	fixed at 57600 bps
	RS 232/RS 422;	9600 bps
		19200 bps
		38400 bps
• Communication range	wired up to 300 m (990 ft)	
	wireless up to 100 m (330ft)	
	any number between 1 and 255	
• Address	any number between 1 and 255	
	6x NiCd AA rechargeable batteries (included)	
	or standard batteries	
	15 DC adaptor	
• Power supply	2 charging modes: via external charger or via XLR port of the projector	
	battery mode	- power save mode after 2 minutes of inactivity
		- automatically switched off after 10 minutes of inactivity
• Temperature range	-15 - 70° c (5F - 158F)	
• Weight	remote control: 1,3 kg (2,8 lbs)	
	receiver: 0,3 kg (0,6 lbs)	

• Order information

Wired Rugged Remote	R9840170
Wireless Rugged Remote starters kit (wireless remote + single channel receiver)	R9840176
Wireless Rugged Remote	R9840171
Single channel (RS232) Receiver	R9840172
Upgrade wired to wireless	R9840175
19" rack mount (for 2 remotes)	R9840174

• Dimensions

specifications subject to change without notice



Rugged Remote

Single channel Receiver

Barco Events

Barco Events
Noordlaan 5, 8520 Kuurne
Belgium
Tel. +32 56 36 89 70
Fax +32 56 36 88 24
events.barco.com
email : sales.events@barco.com

Barco Events
3240 Town Point Drive,
Kennesaw, GA 30144
Tel.: (770) 218-3200
Fax: (770) 218-3250
email : bpsmarketing@barco.com

BarcoProjection is an ISO 9001 registered company. The information and data given are typical for the equipment described. However any individual item is subject to change without notice.

n° R599590

BARCO

Full control | Off screen read out

The Rugged Remote is extremely reliable and shockproof. It was designed by professionals for professionals. It's built to last, even in the most demanding rental & staging applications.



Control and diagnosis mode

The remote control operation mode enables control of 6000, SLM and ELM Series projectors.


Even when the user menu on screen is switched off during the show, the off screen read out provides you with the necessary information. By connecting the Rugged Remote to an ELM or SLM lamp house, in the lamp read mode all the specific lamp parameters can be shown.




| Wired or wireless remote

The Rugged Remote is available in a wired and wireless version. Both versions provide two-way communication with one or more projectors...

Wired Remote



Wireless remote + receiver



Fully equipped

Designed with all possible usage situations in mind, this rock solid working partner can also be mounted within a 19" equipment rack. A shoulder strap provides added convenience when climbing trusses.

The handy carrying case contains the following items;

- Rugged Remote
- Charger
- Supplementary mains plugs; UK/US/AUS
- SUBD9 male/female adaptor
- Lamp communication cable
- Shoulder strap
- Manual

