

DP2K-23B

Bright DLP Barco Alchemy Cinema projector for screens up to 23m (75ft)



- **Brightest images, lowest operating cost**
- **Integrated, DCI-compliant, future-proof projector**
- **Combines media server functionalities with Series 3 cinema processing electronics**

The Barco Alchemy DP2K-23B is a bright and fully integrated digital cinema projector for theaters with screens up to 23m (75ft) wide, based on Texas Instruments' 1.2" DLP Cinema® chip, ensuring exceptional image quality for a premium movie experience in 2D and 3D. By merging the projector and media server functionalities into one projector module, the DP2K-23B Barco Alchemy projector is a full-fledged, DCI-compliant projector and media-server solution with on-board storage. Reducing the required hardware, it increases simplicity and reliability. The smart projector even detects potential operational errors and warns users in case of mishaps. Great in TMS environments, it operates stand-alone in single-screen applications. Thanks to the embedded Barco Web Commander user interface, shows can be created and scheduled remotely.

Low cost of ownership

Geared with the integrated Barco Alchemy technology that drives operational and maintenance costs down, the DP2K-23B offers superior image processing, pristine images and ultimate reliability at a low TCO.

Easy maintenance and operation

The DP2K-23B comes with the intuitive 'Barco Web Commander' user interface for easy operation. The projector detects potential operational errors and warns users if, for instance, a scheduled show is missing assets or KDMs. It also has a modular architecture for simple serviceability and higher uptime.

The DP2K-23B projector is also available in a package with a third-party media server and it can be ordered without the Barco Alchemy module as well.

Unique benefits of Barco Alchemy technology

PRODUCT SPECIFICATIONS**DP2K-23B**

Digital MicroMirror Device™	3 x 1.2" DC2K dark metal devices
Native resolution	2048 x 1080 pixels
Housing	Hermetically sealed DMDs and optical assembly
Lamp	1.2kW - 4kW (Xenon lamp)
Light output	24,500 lumens
Screen size	Up to 23 m / 75ft wide
Contrast ratio	2,000:1
Prime lenses	1.25 - 1.45 1.4 - 2.05 1.6 - 2.35 1.8 - 2.8 2.15 - 3.6 2.8 - 5.5
Control I/O	3x Ethernet 8x GPIO (DB 25) 3D interface USB RS-232 interface (DB9)
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x HDMI2.0a (up to 4K 2D 60fps) 3G-SDI inputs 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K Barco Alchemy projectors have the license standard included.
Integrated storage	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCP playlists & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding
Barco Communicator	Projector installation & configuration Projector update & maintenance
Projector diagnostics	via Integrated Media Server via Communicator control software via SNMP agent
Power requirements	220V
Dimensions	604(H) x 754(W) x 1129(D) mm 23.78(H) x 29.69(W) x 44.45(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Weight	133 kg (293 lbs)

PRODUCT SPECIFICATIONS**DP2K-23B**

Ambient temperature	35°C / 95°F Max.
Exhaust airflow	350 – 390 cfm (10 – 11 m ³ /min)
Options	Barco CineMate App (iOS & Android) - free 3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Dual-projector license Live 3D*** *** Software roadmap

Last updated: 01 Sep 2017

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.