

Kurzer Telezoom EN14

2.56–4.1: 1 (SX+) / 2.37–3.79: 1 (WUXGA)



Fokusbereich: 3,0 - 30,0 m

- 2,57 - 4,10 : 1 (SXGA+)
- 2,37 - 3,79 : 1 (1080p)
- 2,37 - 3,79 : 1 (WUXGA)

TECHNISCHE DATEN**KURZER TELEZOOM EN14**

Working F/#	F 2.1-2.72 Motorized Iris F# 2.1-6.5
Zoom ratio	1.6 Motorized zoom and focus
Focal length	49.1-78.6 mm
Focus Range	Standard: 3.0m – 30m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.5 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 2.37-3.79:1■ SXGA+ 2.56-4.1:1■ 720p 2.8-4.49:1■ XGA 3.5-5.6:1
	Image size tolerance +/-5%

Generiert am: 21 Jan 2018

Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät. Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern. Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.