

# FLDX 1.7- 2.5: 1 (EN61)

WUXGA 1.58-2.33:1 WQXGA/4K 1.70-2.50:1 F80: 2,38–3,51: 1 (WQXGA/4K UHD) (F80 erfordert Objektivadapter R9801442)



**TECHNISCHE DATEN****FLDX 1.7- 2.5: 1 (EN61)**

---

Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 2.38 -3.51 : 1 (WQXGA/4K UHD)
Working F/#	F 2.1-2.5 Motorized Iris F# 2.1-6.5 with memory
Zoom ratio	1.47 Motorized zoom and focus with memory
Focal length	33.7-49.54 mm
Focus Range	Standard: 1.5m – 15m
Weight	2.6 kg
Shipping weight	3.1 kg
Throw Ratio	DMD chip WUXGA 1.58-2.33 :1 WQXGA 1.70-2.50 :1 Image size tolerance +/-2%

---

Generiert am: 07 Feb 2019

Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät. Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern. Die aktuelle Version dieser Broschüre finden Sie unter [www.barco.com](http://www.barco.com).