

FLDX 1.2 - 1.7 : 1 (EN63)

WUXGA 1.12-1.58:1 WQXGA/4K 1.20-1.70:1 F80: 1,68–2,38: 1 (WQXGA/4K UHD) (F80 erfordert den FLD/FLD+-Linsenadapter)



TECHNISCHE DATEN**FLDX 1.2 - 1.7 : 1 (EN63)**

Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442.
Working F/#	F 2.4-2.7 Motorized Iris F# 2.4-6.5 with memory
Zoom ratio	1.42 Motorized zoom and focus with memory
Focal length	23.95-34.02 mm
Focus Range	Standard: 1.5m – 15m
Weight	2.8 kg
Shipping weight	3.4 kg
Throw Ratio	DMD chip WUXGA 1.12-1.58 :1 WQXGA 1.20-1.70:1 Image size tolerance +/-2%

Generiert am: 14 May 2020

Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät. Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern. Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.