

S3-4K Jr

Kompakter und kosteneffektiver Event Master Processor



- **Einfache und zuverlässige Einrichtung und Produktion von Shows**
- **Vom Markt geschätzte 4K-Leistung**
- **Zukunftssichere Aktualisierungsmöglichkeiten des gesamten S3-4K-Systems**

Leistungsstarke Features, einfacher Betrieb

- Modulares kartengestütztes Design
- Einfaches Setup mit dem plattformübergreifenden Event Master Toolset, welches eine Schritt-für-Schritt-Konfiguration ermöglicht
- Kann vor Ort gewartet werden und ist bereit für künftige Signalschnittstellen über die modularen Event Master Cards
- Zweifach redundante Stromversorgung für einen sorgenfreien Betrieb (optional)
- Unterstützung für Breitbildüberblendung

TECHNISCHE DATEN

S3-4K JR

Model	NGS-3U
Live effects canvas	10 Megapixels PVW/PGM 20 Megapixels PGM only
Video inputs	8 HD inputs via 2 input cards (Event Master series cards) <ul style="list-style-type: none">Up to 2x 4K inputs - each input card supports up to 4K@60p4x SD/HD/3G SDI2x HDMI 1.4a (297 MHz)2x DisplayPort 1.1 (300 MHz)
Video outputs	8 HD outputs via 2 output cards (Event Master Series Cards) <ul style="list-style-type: none">Up to 1x 4K outputs - each output card supports up to 4K@60 p4x HDMI 1.4a (297 MHz)2x HDMI 1.4a for Multiviewer (297 MHz max) or 4x HDMI 1.4a when used as standard output card
Genlock	Analog reference input/loop on BNC connectors; bi-level and blackburst at SD and tri-level at HD S3D Sync: 4x input Din connector, 2x output Din connector
Program output	4 program outputs configurable as single screens or tiled/blended widescreens Configurable from 4x 2048x1200@60 max to 1x 4096x2400@60 max Independent edge blending/feathering control for all four sides
Scaled Aux outputs	User-definable from 4x 2048x1200@60 to 1x 4K@60 All outputs can be defined as Aux destinations for a total of 8 Aux outputs Output color correction
Mixers	<ul style="list-style-type: none">Native resolution background mixer per output screenIndependent layer transitions or full Preview/Program transitionFlexible layer allocation – 2 mixable or 4 single scalable PIP/key layers assignable to any Program output screen
Still stores	Up to 100 HD or 25 UHD, depending on the import file size.
Layer effects	<ul style="list-style-type: none">Borders (hard, soft, halo) and drop shadowsColor effectsStrobe, H&V flipLuma, chroma and Cut/Fill keys (not all modes support keying)PIP moves via Keyframes
Multiviewer	<ul style="list-style-type: none">Flexible user-definable layoutsMonitor all Inputs and Outputs, including Preview and AuxTwo outputsDedicated hardware same as E2 Event Master Processor
Expandability	Linking is available as an upgrade option
HDCP	HDCP compliance determined by installed cards
Control	<ul style="list-style-type: none">Event Master screen management software for PC or MacEvent Master ControllersWebUIEthernet RJ-45, 1000/100/10 Mbps autosense
Serviceability	<ul style="list-style-type: none">Field-serviceable I/O and processing cards (not hot-swappable)Hot-swappable dual-redundant power supplies
Noise Level	Max 51.3 dB avg. Fans at 100%. Fan speed is software-managed based on operating temperature. Reference ISO 7779
Dimensions	<ul style="list-style-type: none">Height: 13.26 cm / 5.22' 3 RU rack mount unitsWidth: 43.2 cm / 17" without chassis handles, 48.3 cm / 19" with chassis handles attachedDepth: 54 cm / 21.33" overall
Weight	21.3 kg / 47 lbs
Power	Input power: 100-240 VAC 50/60Hz 700W Ships with single power supply. Optional Dual-redundant, hot-swappable power supplies available as upgrade.
Environmental temperature	0-40° C / 32-104 F
Environmental humidity	0-95% non-condensing (non-operating) 0-85% non-condensing (operational)
Warranty	3 years parts and labor

Generiert am: 04 Mar 2021

Die angegebenen Informationen und Daten sind typisch für das beschriebene Gerät. Jede Spezifikation kann sich aber ohne vorherige Ankündigung ändern. Die aktuelle Version dieser Broschüre finden Sie unter www.barco.com.