

# SLite 10

Outdoor LED display solution



**PRODUCT SPECIFICATIONS****SLITE 10**

Visual Resolution	9,3 mm
Physical Resolution	18,6 mm
Brightness	6500 NIT 5000 NIT (calibrated @ 6500°K)
LED configuration	2R, 2G, 1B
Pixel density	11.449/m <sup>2</sup> (1.064/ft <sup>2</sup> ) 6.912/panel
Hor. viewing angle	120° (min.50% brightness)
Vert. viewing angle	60° (min.50% brightness)
Lifetime	50 000 h (full white -half brightness)
Power consumption	maximum: 720 W / Tile average: 180 W / Tile
Weight / Tile	34 Kg / 75 lbs (excluding structure)
Processing	color : 14 bit
Colors	4,4 trillion
Refresh rate	800 Hz minimum (PAL / NTSC)
Temperature range	operating : -20°C - 40°C (-4 -104°F) storage : -20°C - 60°C (-4 -140°F)
Humidity	operating: 10 -99% storage: 10 -99%
D320 input compatibility	S-Video -Composite -YUV -RGB -SDI -HDSDI -Data DVI up to UXGA
Certifications	UL -CE -TUV -FCC Class A
Tile dimensions	width: 896mm (35.3") height: 672mm (26.5") depth: 249mm (9.8")

Last updated: 26 Nov 2019

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.