

# ClickShare Conferencing Button

ClickShare Conferencing Button



- **Iconic ClickShare component**
- **USB-C device to start wireless conferencing and content sharing**
- **Additional Quick Button with collaboration features**
- **Ultra-fast setup**

The ClickShare Conferencing Button instantly gives you access to wireless conferencing, a more immersive, interactive and guest-friendly meeting experience. Set up your remote meeting with your preferred UC solution. Plug in the USB-C device in your laptop, click and in less than 7 seconds, you are automatically connected to meeting room cameras, microphones, soundbars and any other AV peripherals. You get richer audio, have wider views of the room and can add video to your mix.

Join your next Microsoft Teams call with just one click. With either the ClickShare Button or Desktop App, you decide which suits you best. Instantly you connect wirelessly to the camera and speakers in the room for better hybrid meetings. The same is true for your Zoom, Webex or other calls as well.

Wireless conferencing with the ClickShare Button is guest-friendly, anyone can start a videocall and instantly share content in any meeting room. No installation or training needed. Just plug in and go!

With the additional Quick Button you can access the ClickShare to benefit from advanced meeting controls like window selection, pause, ideation, snapshots,...

Alternatively, you can wirelessly conference and share content with the ClickShare Desktop App with additional functionalities for workflow integration at your disposal. Smart, automated intent-based meeting flows like PresentSense, One-Click-Join, HostFlow and ConferenceView, make hybrid meetings intuitive and stress-free. ClickShare Conference matches your digital workplace strategy. Touch or touchless, Button or App. It's your way of working, your decision.

**PRODUCT SPECIFICATIONS****CLICKSHARE CONFERENCING BUTTON**

---

<b>Weight</b>	60 gr -0.132 lb
<b>Frequency band</b>	2.4 GHZ and 5 GHz
<b>Wireless transmission protocol</b>	IEEE 802.11 a/b/g/n/ac
<b>Authentication protocol</b>	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X in network integration mode
<b>Connectors</b>	USB-C type
<b>Dimensions (HxWxD)</b>	14.6 mm x 59.3 mm x 161.39 mm / 0.57" x 2.354" x 6.354"
<b>Power consumption</b>	Powered over USB 5V DC 350mA Typical 500mA Maximum

---

**Last updated: 17 May 2022**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.