

RLM G5i Performer

With its compact design and sealed optics, the RLM G5i Performer is an ideal all-round projector suitable to both the rental as well as staging markets.



PRODUCT SPECIFICATIONS**RLM G5I PERFORMER**

Light output	4500 ANSI Lumen
Resolution	1024 x 768 (native)
Contrast ratio	1000 : 1 (full field)
High contrast mode	Available with special lenses
Brightness uniformity	> 90%
Lamp	2 x 250 W mercury max. lifetime: 1500 hrs typ. lifetime: 1000 hrs min. lifetime: 750 hrs
Noise level (@ 20°C -68°F)	42 dBa
Noise level (@ 40°C -104°F)	46,5 dBa
Ambient temperature	Max 40°C (104°F)
Power consumption	700 W
Mains Voltage	92-240 V
Weight	Projector: 25 kg (56 lbs) Frame: 5 kg (11 lbs)
Dimensions (WxLxH)	705 x 707,8 x 316,5 mm
Light shutter	Standard
Sealed DLP™ core	Standard
ScenergiX	Standard horizontal and vertical electronic edge blending
Seamless Switching	Standard (wipes, fades, ...)
Picture-in-picture	Up to 4 sources simultaneously (2 data, 1 video and 1 SDI)
Digital zoom	Standard
Lens encoders	On zoom and focus (with TLD lenses)
Linked Constant Light Output	not available
Input source compatibility	1600 x 1200 (max. input)
Fixed Inputs	<ul style="list-style-type: none">■ 1x configurable 5 cable (BNC)■ 1x composite Video (BNC)■ 1x S-Video (4-pin DIN)■ 1x analogue RGB (D15 Connector)■ 1x SDI (+ loop through)■ 1x DVI (Digital Visual Interface)
Modular inputs	not available
Control	<ul style="list-style-type: none">■ 1 x RS-232 / 422 IN■ 1 x XLR female (2 way)■ build-in RF remote transceiver (optional)
Order Information	Projector Body: R9010320 Spare Dual Lamp:R9852940

Last updated: 21 Jan 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.