

FLD 2.37 - 3.79 : 1 (EN14)

2.56 - 4.1 : 1 (SX+) / 2.37 - 3.79 : 1 (WUXGA)



Focus range: 3.0 - 30.0 m

- SX+ 2.56-4.10:1
- 1080 / WUXGA 2.37-3.79:1

PRODUCT SPECIFICATIONS**FLD 2.37 - 3.79 : 1 (EN14)**

Working F/#	F 2.1-2.72 Motorized Iris F# 2.1-6.5
Zoom ratio	1.6 Motorized zoom and focus
Focal length	49.1-78.6 mm
Focus Range	Standard: 3.0m – 30m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.5 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 2.37-3.79:1■ SXGA+ 2.56-4.1:1■ 720p 2.8-4.49:1■ XGA 3.5-5.6:1
	Image size tolerance +/-5%

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.