

FLD 2.37 - 3.79 : 1 (EN14)

2.56 - 4.1 : 1 (SX+) / 2.37 - 3.79 : 1 (WUXGA)



Focus range: 3.0 - 30.0 m

- SX+ 2.56-4.10:1
- 1080 / WUXGA 2.37-3.79:1

PRODUCT SPECIFICATIONS**FLD 2.37 - 3.79 : 1 (EN14)**

| | |
|---------------------------|---|
| Working F/# | F 2.1-2.72 Motorized Iris F# 2.1-6.5 |
| Zoom ratio | 1.6 Motorized zoom and focus |
| Focal length | 49.1-78.6 mm |
| Focus Range | Standard: 3.0m – 30m |
| Custom focus range | Extended focus range is available, please contact sales for details |
| Weight | 2.5 kg |
| Throw Ratio | DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 2.37-3.79:1■ SXGA+ 2.56-4.1:1■ 720p 2.8-4.49:1■ XGA 3.5-5.6:1 |
| | Image size tolerance +/-5% |

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.