

# wePresent WiPG-1000

A basic 1080p wireless presentation system offering wireless screen sharing from any device



- **Auto-on for quick presentations during impromptu meetings**
- **Cross platform compatibility, ideal for BYOD environments**
- **Up to 4 users can present simultaneously in fixed screen mode**

WiPG-1000 is the base model presentation solution from the wePresent product line. The entry-level model is packed-full features making it an affordable solution for classrooms, huddle spaces and meeting rooms. WiPG-1000 can connect to your display via HDMI or VGA outputs offering up to 1080p presentations, there's even an audio jack for secondary audio system support.

#### **Present with any device**

In today's Bring Your Own Device environments, cross platform presentations are more important than ever. wePresent makes it easy for users with any device of any type to connect and present their content quickly and easily even without software installation. WiPG-1000 also allows users to share audio/ video content from an iOS device, using Apple's native Airplay protocol.

#### **Multiple users for simultaneous presentations**

Meetings and classrooms come in a variety of sizes. To help manage even the largest environments, wePresent offers interactive presentation and collaboration solutions that allow up to 64 users to connect and participate. All connected users can take turns presenting, fostering a truly collaborative multi-user experience. Using conference control, moderators can select any of the connected participants from the on-screen queue to present, up to 4 at a time.

#### **Flexible connections & networking with security in mind**

WiPG-1000 offers a configurable Wireless Access Point. Broadcast an additional wireless SSID signal for your team or guests to make a connection. The unit offers enterprise level security with SALS20 data encryption, gatekeeper settings, and individualized control over IP settings.

#### **Built in features for interactive experiences**

WiPG-1000 offers on board USB ports to connect a Bluetooth mouse to enable the use of conference controls on screen. For environments with touchscreen displays, WiPG-1000 offers support for touchscreen control.

WiPG-1000 is not available in the United States, Canada and Mexico.

**PRODUCT SPECIFICATIONS****WEPRESENT WIPG-1000**

|                                  |                                                                                                                                                                                                                                                                                                                                                                                                                 |
|----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating system                 | Windows 7, 8, 10 and above<br>macOS X, 10.9 and above<br>Chromebook OS 74 and above<br>Android 4.1 and above<br>iOS 9 and above                                                                                                                                                                                                                                                                                 |
| Native industry standard support | Apple AirPlay                                                                                                                                                                                                                                                                                                                                                                                                   |
| Video Output                     | 1 x HDMI<br>1 x VGA                                                                                                                                                                                                                                                                                                                                                                                             |
| Frame rate                       | up to 30 fps                                                                                                                                                                                                                                                                                                                                                                                                    |
| Output resolution                | up to 1080p                                                                                                                                                                                                                                                                                                                                                                                                     |
| Connected users                  | up to 64                                                                                                                                                                                                                                                                                                                                                                                                        |
| Sources                          | up to 4 simultaneously with fixed screen layout                                                                                                                                                                                                                                                                                                                                                                 |
| Audio Outputs                    | HDMI<br>analog via audio jack 3.5mm                                                                                                                                                                                                                                                                                                                                                                             |
| Authentication protocol          | WEP<br>WPA / WPA2 PSK                                                                                                                                                                                                                                                                                                                                                                                           |
| Wireless transmission protocol   | 2.4G (b/g/n) / 5G (a/n) switchable                                                                                                                                                                                                                                                                                                                                                                              |
| Interfaces                       | 15 pin VGA<br>HDMI<br>RJ-45<br>USB 2.0 (x3)<br>Reset button<br>Stereo phone jack                                                                                                                                                                                                                                                                                                                                |
| Power consumption                | 13.6W [full load power consumption]<br><br>under test conditions:<br><br>· Power source : DC 5V<br>· SW version : 2.2.3.2<br>· HW version : Rev.C(2016/11/07)<br>· USB port : 0.5A load each port(totally 3 ports)<br>· WiFi : 2.4G/11n (project four 1080p videostream)<br>· Ethernet port : ping packet<br>· HDMI : Output 4-in-1 screen<br>· VGA : Output 4-in-1 screen<br>· Phone jack : Connect to speaker |
| Heat dissipation                 | 14.663 BTU/hr                                                                                                                                                                                                                                                                                                                                                                                                   |
| Weight                           | 780 g [with package]<br>260g [without package]                                                                                                                                                                                                                                                                                                                                                                  |
| Dimensions                       | 154.4 x 60.3 x 25mm [without package]<br>216 x 220 x 66 mm [with package]                                                                                                                                                                                                                                                                                                                                       |
| Environmental temperature        | Operation temperature: 0~40<br>Storage Temperature: -10 ~ +70                                                                                                                                                                                                                                                                                                                                                   |
| Environmental humidity           | Operating humidity: [90%<br>Storage humidity: [85%RH                                                                                                                                                                                                                                                                                                                                                            |

Last updated: 16 Dec 2020

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.