

ClickShare CSE-800

Wireless presentation and collaboration system for boardrooms and conference rooms



- **Wireless connection to central screen**
- **Enhanced security features**
- **Up to 8 users on-screen simultaneously**
- **Share from laptop, tablet or smartphone**
- **Moderation, blackboarding and annotation**
- **4K DCI**

The CSE-800 was designed to bring the ClickShare experience to boardrooms, high-end meeting rooms, and conference rooms. Introducing a number of unique features, including simultaneous sharing of up to 8 people, automatic & manual moderation, and blackboarding & annotation, the CSE-800 is the most powerful system in the ClickShare family today. The CSE-800 was designed for enterprise rollouts and offers enhanced security features, a wider range of connectivity options – including AirPlay and Google Cast support for non-HDCP content – and central management.

The power of 2

The CSE-800 features two HDMI inputs and outputs. There is a direct connection with legacy equipment and easy integration with conferencing systems, and two 4K DCI displays can be driven by a single base unit. Furthermore, the 2 network connections allow separate and simultaneous connection to multiple networks (e.g. guest and corporate networks), and provide additional security and convenience for users. Allowing up to 8 persons to share content simultaneously, the CSE-800 ensures connectivity to the central screen and encourages collaboration.

The moderation functionality was specifically designed for use in larger rooms, with multiple people sharing at the same time. To prevent the rapid switching of screens, making the content difficult to follow, a moderator can manually select which content appears on screen and when, ensuring a great experience for all attendees. The moderation function can be switched off at any time, returning the system into ClickShare's normal operating mode, with content being shared upon the click of a button. For user convenience, security features

of the CSE-800 can be set to one of three predefined levels, depending on the company's policies and needs.

ClickShare introduces Touch back function and ideation in your boardrooms. Run any application from your laptop and control it from the screen. With a few touches on the screen, open presentations, share mails, start a video. Focus on audience and content instead of on your presentation tool.

The CSE-800 is also one of the building blocks of the Barco Ideation Wall for interactive and collaborative meetings. By simply combining a Barco UniSee LCD video wall, a specifically designed Touch frame for Barco UniSee and a ClickShare CSE-800 which supports annotation, blackboarding and Touch back function out of the box, you create a single, unified experience in your meeting room allowing you to enjoy both the interactivity features that our wireless collaboration solution ClickShare offers and the seamless viewing experience of Barco UniSee, never seen on LCD video walls before.

PRODUCT SPECIFICATIONS**CLICKSHARE CSE-800**

General specifications	
Operating system	Windows 7/8/8.1/10 32 & 64 bit macOS 10.10/10.11/10.12/10.13/10.14 (Mojave) Android v5 & v6 & v7 & v8 & 8.1 (ClickShare app) iOS 8, 9, 10, 11 & 12 (ClickShare app)
Video outputs	2x HDMI
Video inputs	2x HDMI
Output resolution	4K DCI (4096x2160) @ 60Hz
AirPlay Support	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 12 / Mac OS 10.14
Google Cast Support	Android 8.1 Oreo
Input resolutions	4K DCI (4096x2160) @ 60Hz
Frame rate	Using inputs: Up to 60fps with one input @ 4K Up to 30fps with two inputs @ 4K Using the ClickShare Button or Apps: Up to 30 fps
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Number of sources simultaneous on screen	8 (4 per screen)
Number of simultaneous connections	64
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
Extended desktop	Available (depending on your operating system). May require ClickShare Extension Pack.
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/b/g/n and IEEE 802.15.1
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Connections	2x Ethernet LAN 1Gbit 2x USB 2.0; 2x USB 3.0 (back); 2x USB 3.0 (front) Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard Possible to extend to 5 years
ClickShare Base Unit dimensions	
Dimensions (HxWxD)	46.2mm x 282.3mm x 206.5mm (excl. antennas) / 1.8" x 11.1" x 8.1" 146.4mm x 282.3mm x 206.5mm (incl. antennas) / 5.8" x 11.1" x 8.1"
Power supply	Standard 110/220 V AC plug
Power consumption	Normal operation: 90W under full usage 52W under normal usage (connect 2 HDMI outputs, connect 1 HDMI input, share with 4 people) ECO mode: 30W Networked standby mode: < 1W Deep standby mode: < 0.5W
Weight	2.2kg / 4.85lbs

Last updated: 20 Dec 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.