

# FLX-24

Medium pitch, 24mm transformable LED module



TYPHOON RENTAL



MODULAR



COMPACT



IP65

WATERPROOF

**PRODUCT SPECIFICATIONS****FLX-24**

Brightness	3 cd
Light output	11 lumens
Viewing angle	140 deg. (horizontal and vertical)
Color depth	16-bit/color
LED type	3-in-1 Full Color SMD
Access	front or rear
Socket mount	M3 thread in socket
Pixel mount	click socket, hot-swappable
Ambient temperature	Max 45° C
Diameter	24 mm
Height	31 mm (incl. socket)
Weight	22.5g (incl. socket and 130 mm cable)
Protection rating	IP66 (rating when mated) 24/7 outdoor use: consult Barco Project Management for application notes
max. number of pixels on 1 cable	256
Default cable string	16 pixels, 160 mm pitch, interconnectable 64 pixels, 160 mm pitch, interconnectable
Default strips	S-25: 32 pixels, 25 mm pitch, interconnectable S-50: 16 pixels, 50 mm pitch, interconnectable

Last updated: 24 Feb 2021

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.