

# FLDX 1.7- 2.5: 1 (EN61)

WUXGA 1.58-2.33:1 WQXGA/4K 1.70-2.50:1 F80: 2.38 - 3.51 : 1 (WQXGA/4K UHD) (F80 requires lens adapter R9801442)



**PRODUCT SPECIFICATIONS****FLDX 1.7- 2.5: 1 (EN61)**

---

<b>Platforms</b>	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 2.38 -3.51 : 1 (WQXGA/4K UHD)
<b>Working F/#</b>	F 2.1-2.5 Motorized Iris F# 2.1-6.5 with memory
<b>Zoom ratio</b>	1.47 Motorized zoom and focus with memory
<b>Focal length</b>	33.7-49.54 mm
<b>Focus Range</b>	Standard: 1.5m – 15m
<b>Weight</b>	2.6 kg
<b>Shipping weight</b>	3.1 kg
<b>Throw Ratio</b>	DMD chip WUXGA 1.58-2.33 :1 WQXGA 1.70-2.50 :1 Image size tolerance +/-2%

---

**Last updated: 26 Nov 2019**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.