

# ClickShare CS-100

Stand-alone wireless presentation system for small meeting rooms



- **Wireless connection to central screen**
- **1 user on-screen**
- **Share from laptop, tablet or smartphone**
- **HDMI output**
- **Delivered with 1 Button**

Successful meetings are all about confidence. Confidence in the ideas, confidence in the presentations, but also confidence in the meeting room technology. That is why Barco has developed ClickShare. With this wireless presentation system, users can simply share what's on their laptop or mobile device, on the presentation screen. No cables, no set-up, no waiting to join in.

## Sharing as a basic need

The CS-100 brings the ClickShare experience to small meeting and huddle rooms where sharing content from a laptop or mobile device is a basic need. Anyone – including guests – can connect with one click and share right away, without the need for any training. Users simply plug a USB-powered device – the ClickShare Button – into their PC or Mac and click the button to get the content from their laptop on the large meeting room screen. With the ClickShare App, users can also share content from their mobile phones or tablets.

## A stand-alone model

The CS-100 is a stand-alone model with an HDMI output, that allows up to 8 users to connect and, with one user sharing at a time. The CS-100 includes the standard ClickShare security features including encryption, login management, https and the possibility to hide the SSID of the Base Unit's wireless network.

The CS-100 is an ISO 27001 certified product.

**PRODUCT SPECIFICATIONS****CLICKSHARE CS-100**

| <b>General specifications</b>            |  |
|--|--|
| Operating system                         | Windows 7/8/8.1/10 32 & 64 bit<br>macOS 10.10/10.11/10.12/10.13 (High Sierra)<br>Android v5 & v6 & v7 & v8 & 8.1 (ClickShare app)<br>iOS 8, 9 & 10 & 11 (ClickShare app) |
| Video outputs                            | 1x HDMI  |
| Frame rate                               | Up to 30 fps   |
| Output resolution                        | 1920x1080  |
| Noise Level                              | Fanless  |
| Number of sources simultaneous on screen | 1  |
| Number of simultaneous connections       | 8  |
| Audio                                    | Via HDMI, analog via Audio Jack 3.5mm  |
| iPad, iPhone and Android compatibility   | Sharing of documents, browser, camera for both Android and iOS devices ClickShare app  |
| Extended desktop                         | Available (depending on your operating system). May require ClickShare Extension Pack.   |
| Authentication protocol                  | WPA2-PSK in stand alone mode   |
| Wireless transmission protocol           | IEEE 802.11 a/g/n  |
| Reach                                    | Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit   |
| Frequency band                           | 2.4 GHZ and 5 GHz (DFS channels not supported)   |
| Connections                              | 1x Ethernet LAN 100Mbit<br>1x (back) + 1x (front) USB<br>Audio analog line out on mini jack socket (3.5mm)   |
| Temperature range                        | Operating: 0°C to +40°C (+32°F to +104°F)<br>Max: 35°C (95°F) at 3000m<br>Storage: -20°C to +60°C (-4°F to +140°F)   |
| Humidity                                 | Storage: 0 to 90% relative humidity, non-condensing<br>Operation: 0 to 85% relative humidity, non-condensing   |
| Anti-theft system                        | Kensington lock  |
| Certifications                           | FCC/CE   |
| Warranty                                 | 3 years standard   |
| Google Cast Support                      | Google Cast not supported  |
| <b>ClickShare Base Unit dimensions</b>   |  |
| Weight                                   | 600g / 1.32lbs   |
| Dimensions (HxWxD)                       | 205mm x 115mm x 45mm (Min.) / 8.1" x 4.5" x 1.8" (Min.)  |
| Power consumption                        | Operation: 6W (typical) / 18W (max)<br>Standby: 2.6W (ECO standby) / 0.4W (Deep standby)   |

Last updated: 07 Feb 2019

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.