

TransForm NDN-220 Pro

Networked Display Node



Barco's TransForm N Networked Display Node is a powerful PC-based networked graphics processor. It is used in the networked visualization environment of a TransForm N system and can display encoded streams coming from the Gbit Ethernet/IP network. H-264, V2D and ProServer represent just the top of a long list of supported codecs and streaming formats. Furthermore, the display controller also has a high-end graphics card to perform the rendering operations as are requested by the TransForm N management clients in the network.

High density content – Large display walls

The NDN-220 Pro Output nodes can display high density content and can drive up to sixteen HD displays with a single node. The unit supports multiple different types of displays including the whole range of Barco display solutions like RPC, LCD & LED.

Managed by CMS inside the TransForm N system multiple NDN-220 Pro output nodes can be combined in a wall-cluster to show a composed synchronized picture on display walls of virtually unlimited size. The NDN-220 Pro offers a dedicated sync-cable based full frame-lock synchronization between up to 30 nodes suiting the needs of video-walls with advanced synchronization requirements.

Features:

- 4 DisplayPort 1.2 outputs
- Up to 4K-UHD resolution per output
- Universal IP video streaming decoding

- Most extensive list of supported codecs and formats
- Network-based content synchronization between multiple display nodes driving a single wall
- Frame lock between multiple display nodes
- Redundant network interface
- Silent operation in a compact and flexible form factor
- Mature Barco quality, robust and reliable

PRODUCT SPECIFICATIONS**TRANSFORM NDN-220 PRO**

| | |
|-------------------|--|
| Memory | 8 GB |
| Disk drive | 128 GB Solid-State Disk SSD |
| Network | 2x 1Gb/s LAN |
| Graphics card | Professional high-performance NVIDIA Quadro-series graphic card |
| Processor | Intel(R) Core(TM) i5-9500E 6-core processor 3.0GHz (4.2GHz max. Turbo frequency) |
| Output | 4x Display Port 1.2 (supporting up to 4x 4K-UHD) 4x DVI-SL via included adapters (supporting up to 4x HD) |
| Input | H.264, MPEG-2/4, V2D, H.263, VNC, Pro-Server (see supported codec list) |
| Form factor | 3U ½ 19" Rackmount housing |
| Dimensions | 131.5mm x 220mm x 305mm 5.18" x 8.66" x 12.01" |
| Weight | 6.1 kg (7.9 kg incl. packaging) |
| Power supply | 100-240V, 8-4A, 50/60Hz |
| Power consumption | 270 W (max) |
| Temperature range | 0° -40°C 32° -104°F |
| Humidity | Max. 80% (noncondensing) |
| Altitude | Up to 5000m (operation) |
| Noise Level | Max. 35dbA (measured at 1m/32.8ft distance at 22°/72) |
| Compliance | CE, UKCA, CB/UL 60950/62368-1, ICES, CCC, FCC Class A Regulatory Model Id: P220 |
| Order Information | R9822000 NDN-220 PRO Display Node (no power cable) R9822000B NDN-220 PRO Display Node (US) R9822000D NDN-220 PRO Display Node (IN) R9822000F NDN-220 PRO Display Node (EU) R9822000G NDN-220 PRO Display Node (UK) R9822000I NDN-220 PRO Display Node (CN) R9822000X NDN-220 PRO Display Node (C13/C14 power cable) R9821099 Rackmount kit for 2x NDN-220 PRO/LITE R766042 Pedestal mount kit for NDN-220 PRO/LITE |

Last updated: 16 Jun 2022

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.