

TLD+ lens (1.14:1 WUXGA) (1.23:1 SXGA+)



PRODUCT SPECIFICATIONS**TLD+ LENS (1.14:1 WUXGA) (1.23:1 SXGA+)**

Motorized Zoom	Not applicable
Motorized Focus	No
Throw Ratio	1.2 : 1
Lens Shift Horizontal	On SLM G5/G8 Left 64% 64% Right On SLM R6/R8 Left 59% 59% Right
Lens Shift Vertical	On SLM G5/G8 Up 100% 20% Down On SLM R6/R8 Up 84% 20% Down

Last updated: 24 Feb 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.