

# DP2K-15C

Compact DLP Barco Alchemy Cinema projector for screens up to 15m (49ft)



- **Small footprint, budget-friendly performance**
- **Integrated, DCI-compliant, future-proof projector**
- **Combines media server functionalities with Series 3 cinema processing electronics**

The Barco Alchemy DP2K-15C is a compact and fully integrated digital cinema projector for mid-size theaters with screens up to 15m (49ft) wide, based on Texas Instruments' 0.98" DLP Cinema® chip. It ensures a first-class movie experience with consistent picture brightness, rich contrast and vibrant colors. By merging the projector and media server functionalities into one projector module, the Barco Alchemy DP2K-15C is a full-fledged, DCI-compliant projector and media-server solution with on-board storage. Reducing the required hardware, it increases simplicity and reliability. Truly smart, it detects potential operational errors and warns users about mishaps. Great in TMS environments, it operates stand-alone in single-screen applications. Thanks to the embedded Barco Web Commander user interface, shows can be created and scheduled remotely.

### **Low cost of ownership**

Geared with the integrated Barco Alchemy technology that drives operational and maintenance costs down, the DP2K-15C offers superior image processing, pristine images and ultimate reliability at a low TCO.

### **Easy maintenance and operation**

The DP2K-15C comes with the 'Barco Web Commander' screen management system featuring an intuitive user interface. The projector detects potential operational errors and warns users in case of mishaps. It also has a fully modular architecture for simple serviceability and higher uptime.

The DP2K-15C projector is also available in a package with a third-party media server and it can be ordered without the Barco Alchemy module as well.

### **Unique benefits of Barco Alchemy technology**

**PRODUCT SPECIFICATIONS****DP2K-15C**

Digital MicroMirror Device™	3 x 0.98" DC2K dark metal devices
Native resolution	2,048 x 1,080 pixels
Housing	Hermetically sealed DMDs and optical assembly
Lamp	1.2kW - 3kW
Light output	14,500 lumens
Screen size	Up to 15m / 49ft wide (screen gain 1.4 @ 14 ftl)
Contrast ratio	2,000:1
Prime lenses	1.2 - 1.8 1.4 - 2.05 1.6 - 2.5 1.95 - 3.2 2.4 - 3.9
Control I/O	3x Ethernet 8x GPIO (DB 25) 3D interface USB RS-232 interface (DB9)
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x HDMI2.0a (up to 4K 2D 60fps) 2x 3G-SDI inputs 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K Barco Alchemy projectors have the license standard included.
Integrated storage	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCP playlists & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding
Barco Communicator	Projector installation & configuration Projector update & maintenance
Projector diagnostics	via Integrated Media Server via Communicator control software via SNMP agent
Power requirements	220V
Dimensions	558(H) x 694(W) x 1034(D) mm 22.0(H) x 27.3(W) x 40.7(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Weight	102kg (225lbs)

**PRODUCT SPECIFICATIONS****DP2K-15C**

---

Ambient temperature	35°C / 95°F Max.
Exhaust airflow	240 – 280 cfm (6,8 – 8 m <sup>3</sup> /min)
Options	Barco CineMate App (iOS & Android) - free 3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Dual-projector license Live 3D*** ** In testing *** Software roadmap

---

Last updated: 21 Jan 2018

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.