

FLD lens (0.74 : 1) EN12 (optimized for WUXGA)



- WUXGA = 0.74 : 1 (F70 W, F90 W)
- 1080p = 0.79 : 1
- SXGA+ = 0.86 : 1
- 720p = 0.94 : 1
- XGA = 1.17 : 1

PRODUCT SPECIFICATIONS**FLD LENS (0.74 : 1) EN12 (OPTIMIZED FOR WUXGA RESOLUTION)**

Working F/#	F 2.1 Motorized Iris F# 2.1-6.5
Zoom ratio	No zoom Motorized focus
Focal length	16.35 mm @ 1.15m projection distance
Focus Range	Standard: 0.5m – 5m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	1.9 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/Wuxga 0.74:1■ SXGA+ 0.81:1■ 720p 0.93:1■ XGA 1.17:1
	Image size tolerance +/-5%

Last updated: 03 Sep 2020

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.