

FLD lens (0.74 : 1) EN15 (optimized for WUXGA)



- WUXGA = 1.16 : 1 (F70 W, F90 W)
- 1080p = 1.16 : 1
- SXGA+ = 1.26 : 1
- 720p = 1.37 : 1
- XGA = 1.72 : 1

PRODUCT SPECIFICATIONS**FLD LENS (0.74 : 1) EN15 (OPTIMIZED FOR WUXGA RESOLUTION)**

Working F/#	F 2.1 Motorized Iris F# 2.1-6.5
Zoom ratio	No zoom Motorized focus
Focal length	23.98 mm
Focus Range	Standard: 1.5m – 15m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.4 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ 1080p/WUXGA 1.16:1■ SXGA+ 1.25:1■ 720p 1.37:1■ XGA 1.71:1
	Image size tolerance +/-5%

Last updated: 03 Sep 2020

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.