

# FLD 1:16 : 1 (EN15)

1.25 : 1 (SX+) / 1.16 : 1 (WUXGA)



Focus range: 1.5 - 15.0 m

Throw ratio

- SX+ 1.25:1
- 1080 / WUXGA 1.16:1

**PRODUCT SPECIFICATIONS****FLD 1:16 : 1 (EN15)**

---

Working F/#	F 2.1 Motorized Iris F# 2.1-6.5
Zoom ratio	No zoom Motorized focus
Focal length	23.98 mm
Focus Range	Standard: 1.5m – 15m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.4 kg
Throw Ratio	DMD chip <ul style="list-style-type: none"><li>■ 1080p/WUXGA 1.16:1</li><li>■ SXGA+ 1.25:1</li><li>■ 720p 1.37:1</li><li>■ XGA 1.71:1</li></ul>
	Image size tolerance +/-5%

---

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.