

ClickShare CSE-200

Wireless presentation system for small to medium sized meeting rooms



- **Wireless connection to central screen**
- **Up to 2 users on-screen**
- **Share from laptop, tablet or smartphone**
- **Enhanced security features**
- **Touch back support**
- **Central management**
- **Delivered with 2 Buttons**

Creativity is one of the core assets of your organization. With ClickShare, you can make sure ideas receive the attention they deserve. This wireless presentation system allows users to simply share what's on their laptop or mobile device, on the presentation screen. No cables, no set-up, no waiting to join in.

Plug in to stand out

The CSE-200 offers the ClickShare experience for small and medium-sized meeting rooms. Anyone – including guests – can connect with one click and share right away, without the need for any training. Users simply plug a USB-powered device – the ClickShare Button – into their PC or Mac and click the button to get the content from their laptop on the large meeting room screen. With the ClickShare Apps, users can also share content from their laptops, mobile phones or tablets. Make sure to have firmware version 1.7 installed on your Base Unit to enable the best experience with the Desktop App.

Encouraging collaboration

The CSE-200 was designed for enterprise rollouts and offers enhanced security features, a wider range of connectivity options – including AirPlay and Google Cast support for non-HDCP content – Touch back function and central management. Allowing up to 2 persons to share content simultaneously, the CSE-200 ensures direct connectivity to the central screen and encourages collaboration. For user convenience, security features of the CSE-200 can be set to one of three predefined levels, depending on the company's policies and needs. Last but not least, the device's API also makes integration into the company network a lot easier. ClickShare also enables the touch back function in your meeting rooms. Run any application from your laptop and control it from the screen. With a few touches on the screen, open presentations, share mails, start a video. Focus on audience and content instead of on your presentation tool.

The CSE-200 is an ISO 27001 certified product.

PRODUCT SPECIFICATIONS**CLICKSHARE CSE-200**

ClickShare Base Unit dimensions	
Dimensions (HxWxD)	205mm x 115mm x 45mm (excl. antennas) / 8.1" x 4.5" x 1.8" 205mm x 150mm x 135mm (incl. antennas) / 8.1" x 5.9" x 5.3"
Power supply	Standard 110/220 V AC plug or Power over Ethernet (PoE Plus)
Power consumption	Operation: 6W (typical) / 18W (max) Standby: 2.6W (ECO standby) / 0.4W (Deep standby)
Weight	600g / 1.32lbs
General specifications	
Operating system	Windows 7/8/8.1/10 32 & 64 bit macOS 10.12/10.13/10.14 (Mojave) Android v7 & v8 & 8.1 (ClickShare app) iOS 10, 11 & 12 (ClickShare app)
Video outputs	1x HDMI
AirPlay Support	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 12/ Mac OS 10.14
Google Cast Support	Android 8.1 Oreo
Frame rate	Up to 30 fps
Output resolution	1920x1080
Noise Level	Fanless
Number of sources simultaneous on screen	2
Number of simultaneous connections	16
Audio	Via HDMI, analog via Audio Jack 3.5mm, S/PDIF
iPad, iPhone and Android compatibility	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
Extended desktop	Available (depending on your operating system). May require ClickShare Extension Pack.
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
Frequency band	2.4 GHz and 5 GHz (DFS channels not supported)
Connections	1x Ethernet LAN 100Mbit 2x (back) + 1x (front) USB Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Warranty	3 years standard Possible to extend to 5 years

Last updated: 13 Jun 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.