

# ClickShare CSE-200

Wireless presentation system for small to medium sized meeting rooms



- **Wireless connection to central screen**
- **Up to 2 users on-screen**
- **Share from laptop, tablet or smartphone**
- **Enhanced security features**
- **Touch back support**
- **Central management**
- **Delivered with 2 Buttons**

Creativity is one of the core assets of your organization. With ClickShare, you can make sure ideas receive the attention they deserve. This wireless presentation system allows users to simply share what's on their laptop or mobile device, on the presentation screen. No cables, no set-up, no waiting to join in.

## **Plug in to stand out**

The CSE-200 offers the ClickShare experience for small and medium-sized meeting rooms. Anyone – including guests – can connect with one click and share right away, without the need for any training. Users simply plug a USB-powered device – the ClickShare Button – into their PC or Mac and click the button to get the content from their laptop on the large meeting room screen. With the ClickShare App, users can also share content from their mobile phones or tablets.

## **Encouraging collaboration**

The CSE-200 was designed for enterprise rollouts and offers enhanced security features, a wider range of connectivity options – including AirPlay and Google Cast support for non-HDCP content – Touch back function and central management. Allowing up to 2 persons to share content simultaneously, the CSE-200 ensures direct connectivity to the central screen and encourages collaboration. For user convenience, security features of the CSE-200 can be set to one of three predefined levels, depending on the company's policies and needs. Last but not least, the device's API also makes integration into the company network a lot easier. ClickShare also enables the touch back function in your meeting rooms. Run any application from your laptop and control it from the screen. With a few touches on the screen, open presentations, share mails, start a video. Focus on audience and content instead of on your presentation tool.

**PRODUCT SPECIFICATIONS****CLICKSHARE CSE-200**

<b>ClickShare Base Unit dimensions</b>	
<b>Dimensions (HxWxD)</b>	205mm x 115mm x 45mm (excl. antennas) / 8.1" x 4.5" x 1.8" 205mm x 150mm x 135mm (incl. antennas) / 8.1" x 5.9" x 5.3"
<b>Power supply</b>	Standard 110/220 V AC plug or Power over Ethernet (PoE Plus)
<b>Power consumption</b>	Operation: 6W (typical) / 18W (max) Standby: 2.6W (ECO standby) / 0.4W (Deep standby)
<b>Weight</b>	600g / 1.32lbs
<b>General specifications</b>	
<b>Operating system</b>	Windows 7/8/8.1/10 32 & 64 bit macOS 10.10/10.11/10.12/10.13/10.14 (Mojave) Android v5 & v6 & v7 & v8 & 8.1 (ClickShare app) iOS 8, 9, 10, 11& 12 (ClickShare app)
<b>Video outputs</b>	1x HDMI
<b>AirPlay Support</b>	iOS mirroring (AirPlay) from iOS 9.0 up to iOS 12/ Mac OS 10.14
<b>Google Cast Support</b>	Android 8.1 Oreo
<b>Frame rate</b>	Up to 30 fps
<b>Output resolution</b>	1920x1080
<b>Noise Level</b>	Fanless
<b>Number of sources simultaneous on screen</b>	2
<b>Number of simultaneous connections</b>	16
<b>Audio</b>	Via HDMI, analog via Audio Jack 3.5mm, S/PDIF
<b>iPad, iPhone and Android compatibility</b>	Sharing of documents, browser, camera for both Android and iOS devices via ClickShare app
<b>Extended desktop</b>	Available (depending on your operating system). May require ClickShare Extension Pack.
<b>Authentication protocol</b>	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X in network integration mode
<b>Wireless transmission protocol</b>	IEEE 802.11 a/g/n
<b>Reach</b>	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit
<b>Frequency band</b>	2.4 GHz and 5 GHz (DFS channels not supported)
<b>Connections</b>	1x Ethernet LAN 2x (back) + 1x (front) USB Audio analog line out on mini jack socket (3.5mm), digital S/PDIF
<b>Temperature range</b>	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
<b>Humidity</b>	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
<b>Anti-theft system</b>	Kensington lock
<b>Certifications</b>	FCC/CE
<b>Warranty</b>	3 years standard Possible to extend to 5 years

**Last updated: 28 Nov 2018**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.