

# FLD+ Short Focus 0.8 - 1.21 : 1 (EN46)



- Focus range: 0.7 - 7.0 m
- Throw ratio
  - 0.80 - 1.21 : 1 (WQXGA)
- 0.80 - 1.21 : 1 (WQXGA)
  - 0.80 - 1.21 : 1 (panorama)
- 0.80 - 1.21 : 1 (panorama)
  - 0.75 - 1.13 : 1 (WUXGA)
- 0.75 - 1.13 : 1 (WUXGA)
  - 0.75 - 1.13 : 1 (1080p)
- 0.75 - 1.13 : 1 (1080p)

**PRODUCT SPECIFICATIONS****FLD+ SHORT FOCUS 0.8 - 1.21 : 1 (EN46)**

---

<b>Working F/#</b>	F 2.4-3.29 Motorized Iris F# 2.4-6.5
<b>Zoom ratio</b>	1.51 Motorized zoom and focus
<b>Focal length</b>	15.98-23.99 mm
<b>Focus Range</b>	Optical Performance 0.7-7.0 m
<b>Custom focus range</b>	Extended focus range is available, please contact sales for details
<b>Weight</b>	3.14 kg
<b>Throw Ratio</b>	DMD chip <ul style="list-style-type: none"><li>■ WQXGA 0.80 - 1.21 : 1</li><li>■ 1080p /WUXGA 0.75 - 1.13 : 1</li><li>■ SXGA+ 0.81 - 1.22 : 1</li><li>■ Image size tolerance +/- 2%</li></ul>

---

**Last updated: 15 Oct 2020**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.