

FLD+ Short Focus 0.8 - 1.21 : 1 (EN46)



- Focus range: 0.7 - 7.0 m
- Throw ratio
 - 0.80 - 1.21 : 1 (WQXGA)
- 0.80 - 1.21 : 1 (WQXGA)
 - 0.80 - 1.21 : 1 (panorama)
- 0.80 - 1.21 : 1 (panorama)
 - 0.75 - 1.13 : 1 (WUXGA)
- 0.75 - 1.13 : 1 (WUXGA)
 - 0.75 - 1.13 : 1 (1080p)
- 0.75 - 1.13 : 1 (1080p)

PRODUCT SPECIFICATIONS**FLD+ SHORT FOCUS 0.8 - 1.21 : 1 (EN46)**

Working F/#	F 2.4-3.29 Motorized Iris F# 2.4-6.5
Zoom ratio	1.51 Motorized zoom and focus
Focal length	15.98-23.99 mm
Focus Range	Optical Performance 0.7-7.0 m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	3.14 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ WQXGA 0.80 - 1.21 : 1■ 1080p /WUXGA 0.75 - 1.13 : 1■ SXGA+ 0.81 - 1.22 : 1■ Image size tolerance +/- 2%

Last updated: 29 Sep 2020

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.