

# DP4K-32B

Bright 4K Barco Alchemy DLP Cinema projector for screens up to 32m (105ft)



- **4K resolution, premium movie experience**
- **Integrated, DCI-compliant, future-proof projector**
- **Combines media server functionalities with Series 3 cinema processing electronics**

The Barco DP4K-32B is a bright 4K cinema projector for screens up to 32m (105ft). Featuring TI's 1.38" DLP Cinema® chip, the DP4K-32B offers stunning 4K images with superb brightness and vibrant colors to ensure a razor-sharp movie experience on premium cinema screens. By merging the projector and media server functionalities into one projector module, the DP4K-32B Barco Alchemy projector is a full-fledged, DCI-compliant projector and media-server solution with on-board storage. Reducing the required hardware, it increases simplicity and reliability. The smart projector even detects potential operational errors and warns users in case of mishaps. Great in TMS environments, it operates stand-alone in single-screen applications. Thanks to the embedded Barco Web Commander user interface, shows can be created and scheduled remotely.

### **Future-proof technology for an enthralling movie experience**

A single DP4K-32B Barco Alchemy projector can truly elevate the movie experience by enabling 4K 2D to be shown at 60 fps and 4K 3D images. It also shows uncompressed 4K 60 fps alternative content for crisp images.

### **Low cost of ownership**

Geared with integrated Barco Alchemy technology that drives operational and maintenance costs down, the DP4K-32B offers superior image processing, pristine images and ultimate reliability at a low TCO.

The DP4K-32B projector is also available in a package with a third-party media server and it can be ordered without the Barco Alchemy module as well.

### **Unique benefits of Barco Alchemy technology**

**PRODUCT SPECIFICATIONS****DP4K-32B**

Digital MicroMirror Device™	3 x 1.38" DC4K dark metal devices
Native resolution	4,096 x 2,160 pixels
Housing	Hermetically sealed DMDs and optical assembly
Lamp	3kW - 7kW (Xenon lamp)
Light output	33,000 lumens (6.5kW lamp factory installed) (more than 34,000 lumens using 7kW lamp)
Screen size	Up to 32m / 105 ft wide
Contrast ratio	1,850:1
Control I/O	3x Ethernet 8x GPIO (DB 25) 3D interface USB RS-232 interface (DB9)
Integrated Cinema Media Processor	DCI 4K 2D up to 60fps* DCI 4K 3D (24 or 30 fps per eye)* DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x HDMI2.0a (up to 4K 2D 60fps) 2x 3G-SDI inputs 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10 * 4K 24fps is standard. For 4K 60 fps / 4K 3D on ICMP upgrade modules a license is required. Newly-built 4K BarcoAlchemy projectors have the license standard included.
Integrated storage	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
Barco Web Commander	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest Dynamic DCp playlist & intermission TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets Dual projector 3D: passive and active Auro 11.1 decoding
Power requirements	3W+N+PE 230/400V 16A 50-60Hz or 3W+PE 208V 27A 50-60Hz 30,000 BTU/hr (with 6.5kW - 7kW lamp)
Dimensions	604(H) x 754(W) x 1129(D) mm / 23.78(H) x 29.69(W) x 44.45(D) inch NB.: min. 5 cm of air inlet spacing required at the bottom of projector
Weight	141 kg (311 lbs)
Ambient temperature	35°C / 95°F Max.
Exhaust airflow	350 – 390 cfm (10 – 11 m <sup>3</sup> /min)
Standard Features	CLO (Constant Light Output) Powerful SNMP agent Motorized/memorized lens (focus, zoom & shift) Advanced patented DMD cooling

## PRODUCT SPECIFICATIONS

## DP4K-32B

### Options

Barco CineMate App (iOS & Android) - free  
3D add-ons  
Touch screen monitor, inc. Barco Commander & Communicator  
Pedestal  
CineCare Web  
Auro 11.1 license  
Barco Escape license  
Dual projection license  
4K 60p / 4K 3D license (included)  
Live 3D\*\*\*  
\*\*\* Software roadmap

Last updated: 24 Nov 2017

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.