


NX6 (fixed installation)

6mm pixel pitch, 2,000 nits, true black indoor LED display



Thanks to its black LED, the NX6 delivers more contrast and deeper black levels than any other product on the market. Black LED is only one element that makes the NX6 unique. Key advances in base materials, mechanical design and color processing have raised the bar of LED displays to new heights of image quality.

- Phenomenal black levels
- 4,200:1 contrast ratio
- 2,000 nits brightness
- 16-bit color processing
- Replaceable shaders
- Consistent uniformity
- High Definition-ready
- Modular creativity

PRODUCT SPECIFICATIONS**NX6 (FIXED INSTALLATION)**

| | |
|-------------------------|--|
| Pixel pitch | 6.22 mm |
| Brightness | 2,000 nits |
| LED configuration | 3-in-1 SMD |
| Pixel density | 25,829/sqm 2,402/sqf 5,832/tile (72x81) |
| Hor. viewing angle | 120° |
| Vert. viewing angle | +60°, -60° (@ 50% brightness) |
| Contrast ratio | 4,200:1 (at 500 lux) |
| Lifetime | 60,000 hours to 75% of initial brightness |
| Power consumption | 219 W/tile (max) 104 W average |
| Operation power voltage | 200-240V / 50-60Hz |
| Tile dimensions | Width: 448mm (17.6") Height: 504mm (19.8") Depth: 228.6mm (9") |
| Weight / Tile | 13.8 kg/30.3 lbs |
| IP rating | Indoor use only |

Last updated: 26 Nov 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.