

FLDX 0.8 - 1.21 : 1 (EN66)

Short focus



PRODUCT SPECIFICATIONS**FLDX 0.8 - 1.21 : 1 (EN66) SHORT FOCUS**

Platforms	For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 1.12 -1.70 : 1 (WQXGA/4K UHD)
Working F/#	F 2.4-3.29 Motorized Iris F# 2.4-6.5 with memory
Zoom ratio	1.51 Motorized zoom and focus with memory
Focal length	15.98-23.99 mm
Focus Range	0.7-7.0 m
Weight	3.3 kg
Shipping weight	4.0 kg
Throw Ratio	DMD chip WUXGA 0.75 -1.13 : 1 WQXGA 0.80 -1.21 : 1 Image size tolerance +/-2%

Last updated: 24 Feb 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.