

FLDX 0.8 - 1.21 : 1 (EN66)

Short focus



PRODUCT SPECIFICATIONS**FLDX 0.8 - 1.21 : 1 (EN66) SHORT FOCUS**

| | |
|------------------------|---|
| Platforms | For F35, FL40, F70, F80* and F90 projector series *requires lens adapter R9801442. F80 specific throw ratio: 1.12 -1.70 : 1 (WQXGA/4K UHD) |
| Working F/# | F 2.4-3.29 Motorized Iris F# 2.4-6.5 with memory |
| Zoom ratio | 1.51 Motorized zoom and focus with memory |
| Focal length | 15.98-23.99 mm |
| Focus Range | 0.7-7.0 m |
| Weight | 3.3 kg |
| Shipping weight | 4.0 kg |
| Throw Ratio | DMD chip WUXGA 0.75 -1.13 : 1 WQXGA 0.80 -1.21 : 1 Image size tolerance +/-2% |

Last updated: 02 Sep 2020

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.