

SLM R10 Performer

A Compact Projector for Rental & Staging Applications



PRODUCT SPECIFICATIONS**SLM R10 PERFORMER**

| | |
|---------------------------------|---|
| Light output | 10.000 ANSI Lumen |
| Digital MicroMirror Device™ | 3 high resolution SXGA DMD™s |
| Resolution | 1280 x 1024 (native) 1600 x 1200 (max) |
| Brightness uniformity | 90 % |
| Contrast | Normal mode: 800 : 1 High mode: 1600 : 1 (Full White/Full Black) |
| Lamp | Lifetime (max): 1000 Hrs Lifetime (typ): 500 Hrs Lamp power: 2,2 kW |
| Noise level (@ 20°C -68°F) | < 56 |
| Noise level (@ 40°C -104°F) | < 58 |
| Mains Voltage | 200-240 V |
| Power consumption | 2750 W |
| Ambient temperature | 35°C (95 F) |
| Size | 875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9" |
| Weight (including rigging gear) | 57 kg (126 lbs) |
| Lenses | BARCO's "click-and-play™" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions. |
| Lens Shift | Motorized V shift: up to 100% Motorized H shift: up to 65% |
| Sealed DLP™ core | No |
| Seamless Switching | Standard |
| ScenergiX | Standard |
| Network connection | Optional |
| Fixed Inputs | · 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals · 2 Multistandard DVI · SDI input (Serial Digital Input) |
| Optional Inputs | One free digital input slot for optional input modules: · SDI · HD -SDI |
| Remote control | • RS232 or RS422 loop-through input (D9-connector) for PC based projector control • Communication input (D9-connector) for peripherals • 3 pin male XLR connector for wired remote (standard remote) • 3 pin female XLR connector for bi-directional communication (rugged remote) |

Last updated: 21 Jan 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.