

ClickShare C-10

Making presentation flow in medium-sized and large meeting rooms



- Full BYOD support
- Seamless content sharing with Button or Desktop App
- Enhanced security, connected and cloud managed
- Full interactivity with touch back, blackboarding, annotation
- Delivered with 1 Button

Technology can help to make meeting participants engaged, inspired and active. ClickShare C-10 adds interactive features to full BYOD, easy wireless presentation in any medium to large meeting room. It is the wireless presentation hub that makes your meetings flow with one click in the ClickShare Button or ClickShare App, from any laptop or mobile device.

Find out what's new in the latest ClickShare update

Full BYOD content sharing

With the ClickShare C-10, you can start a meeting and get your content on screen within seconds. No matter the device you are using. Plug & Play with the ClickShare Button, that works perfectly on both pc or Mac. Go for workflow integration with the ClickShare App on laptop, mobile or tablet. Or enable full Bring Your Own Device (BYOD) on a 4K canvas: screen mirroring with Airplay, GoogleCast and Miracast works flawlessly.

Anyone, including guests, can share content wirelessly to the central room display with our one-click meeting experience. Two users can share side by side in full HD on screen. No cables, no software to download, no training needed.

Enjoy interactive, creative meetings

ClickShare C-10 users can benefit from advanced interactive features including local view of the room display, decide what they share (either a full screen or a single window), annotation, blackboarding and touch back support that allows users to control the touchscreen in the room. Designed especially to make meetings richer and more dynamic. C-10 makes hybrid collaboration flow in creative meetings, brainstorming and discussion in one click.



Enhanced security and seamless integration

Designed for enterprise rollouts, the IT-grade C-10 offers you enhanced security features (ISO27001 certified) and a wide range of connectivity options. With the XMS Cloud Management Platform you enjoy remote management of units and clear analytics to drive your digital workplace. For practical questions on network deployment of the ClickShare range, check our technical support or get in touch with your Barco contact.

Boost collaboration in your meeting room

The ClickShare C-10 can be used stand-alone or in combination with your existing conference room. It empowers meetings with simple, one-click wireless content sharing. ClickShare completes the room set-up and makes presentation simple, easy and wireless. Use your display for digital signage content when not used for presenting thanks to signage integration options. Designed to fit your business perfectly and evolve with it. With flexibility for the future built in, it's one of the smartest investments you can make in your meeting room.

You can have ClickShare in your meeting rooms without delay, thanks to strong inventory levels for all models.

PRODUCT SPECIFICATIONS**CLICKSHARE C-10**

General specifications	
Operating system	Windows 10 and higher macOS 11 (BigSur) and higher. Android v9 and higher (ClickShare App)* iOS 12 and higher (ClickShare App)*
Video outputs	4K UHD (3840*2160) @ 30Hz. HDMI 1.4b
Audio output	HDMI
USB	1 X USB-A, 1 X USB-C
ClickShare Buttons	1
ClickShare App	Desktop & Mobile
Native protocols	Airplay, Google Cast, Miracast*
Maximum number of simultaneous connections (with Buttons and/or App)	32
Noise Level	Max. 25dBA @ 0-30°C Max. 30dBA @ 30-40°C
Authentication protocol	WPA2-PSK in stand alone mode WPA2-PSK or IEEE 802.1X using the ClickShare Button in network integration mode
Wireless transmission protocol	IEEE 802.11 a/g/n/ac and IEEE 802.15.1
Reach	Adjustable with signal strength modulation; max. 30m (100 ft) between ClickShare Button and ClickShare Base Unit Frequency band 2.4 GHz and 5 GHz
Frequency band	2.4 GHz and 5 GHz (DFS channels supported in select number of countries)
Connections	1x Ethernet LAN 1Gbit 1x USB Type-C 2.0 (front); 1x USB Type A 2.0 (front)
Temperature range	Operating: 0°C to +40°C (+32°F to +104°F) Max: 35°C (95°F) at 3000m Storage: -20°C to +60°C (-4°F to +140°F)
Humidity	Storage: 0 to 90% relative humidity, non-condensing Operation: 0 to 85% relative humidity, non-condensing
Anti-theft system	Kensington lock
Certifications	FCC/CE
Touch screen support & Interactivity	Yes
Room Dock (peripheral support)	No
Local view	Yes
Network connection	LAN & WiFi
Management and reporting	Yes
Warranty	1 year standard. 5 years coverage via SmartCare
*	* depends on configuration, available in future firmware updates
ClickShare Base Unit dimensions	
Dimensions (HxWxD)	34 mm x 135 mm x 135 mm
Power supply	Standard 110/220 V AC plug
Power consumption	Operational: 5-10W, 24W Max
Weight	900 gr

Last updated: 15 Nov 2022Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.