

Short tele zoom EN24



Focus range: 5.0 - 20.0 m

- SX+ 2.78-4.45:1
- 1080 / WUXGA 2.50-4.00:1

PRODUCT SPECIFICATIONS**SHORT TELE ZOOM EN24**

Working F/#	F 2.6-3.13 Voice coil operated Iris F 2.5-7.0
Zoom ratio	1.6 Motorized zoom and focus
Focal length	53.3-85.3 mm
Focus Range	Standard: 5m – 20m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.9 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ SXGA+ 2.78-4.45:1■ 1080p/WUXGA 2.5-4.0:1

Image size tolerance +/-5%

Last updated: 24 Feb 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.