

# DP-1200

2K Digital cinema projector for screens up to 12m (40ft)



**PRODUCT SPECIFICATIONS****DP-1200**

Digital MicroMirror Device™	3 x 0.98" DC2K dark metal devices
Native resolution	2048 x 1080
Housing	Hermetically sealed DMD™ and optical assembly
Lamp	1.2kW -2kW Xenon lamp size
Screen Width	Screen width (screen gain 1:2) @ 14ft* : up to 12m -40ft (* ) = ± 10% variation possible between units
Contrast ratio	2000:1
Digital Video Inputs	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Prime lenses	1.2-1.8 1.4-2.05 1.6-2.5 1.95-3.2 2.4-3.9
Projector diagnostics	via PC touch panel via Communicator control software via SNMP agent
Power requirements	200–240 VAC, 50–60 Hz, 15 amps at 200 VAC
Dimensions	projector: 505(H) x 689(W) x 1018(D) mm 19.9(H) x 27.1(W) x 40.0(D) inch NB: min. 5 cm of air inlet spacing required at the bottom of projector
Weight	projector: 93kg (205lbs)
Ambient temperature	max. 35°C / 95°F
Options	CLO-constant light output ACS-2048 SNMP agent
Mounting	universal pedestal (optional)

Last updated: 10 Jan 2020

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.