

# SP4K-12

12,000 lumens smart cinema projector



**12K**  
LUMENS

**4K**  
4096X2160



- **Brilliant image**
- **Ready for tomorrow, today**
- **Barco EcoPure™**
- **Fit and forget**

SP4K-12 is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A next-generation laser projection family for all cinema screens. The SP4K models come in many different configurations offering you the freedom of choice. A wide range of brightness options, compatibility with Barco lenses and selected 3rd party lenses, as well as a touch display and live streaming option. Play with the available options to match your specific needs.

## **Brilliant image**

The SP4K models of the Series 4 family brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management™ includes patented technology to guarantee sharp, consistent image quality over time.

## **Ready for tomorrow, today**

With the SP4K models and their RGB laser lightsource, the Barco Colorgenic™ technology opens up more than 98.5% of Rec. 2020. Moreover, all SP4K models are fully enabled for future innovations like 4K 120fps and compatibility with the latest immersive audio standard.

## **Barco EcoPure™**

This silent running projector (50dB(A)) is fully ready for boothless operation. In addition, the SP4K-12 smartly manages its power consumption reaching projector efficiency levels up to 8 lumens per Watt. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

## **Fit and forget**

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate™ spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-12 seamlessly integrates into your current setup.

**PRODUCT SPECIFICATIONS****SP4K-12**

Native brightness	12,000 lumens (typical)
Native contrast ratio	2300:1 (typical) up to 3000:1 with HC lens
Digital MicroMirror Device™	3x 0.98" DC4K TRP
Resolution	native 4K: 4096 x 2160
Color gamut	DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates)
Light source	Laser
Prime lenses	With C-lensholder: 0.8 -1.16; 1.09 -1.40; 1.2 -1.8; 1.4 -2.05; 1.6 -2.5 ; 1.95 -3.2; 2.4 -3.9 With B-lensholder: 1.01; 1.27; 1.6 - 2.4; 1.9 - 2.6; 2.0 - 2.95; 2.3 - 3.65; 2.8 - 4.7; 3.55 - 6.95 High-brightness and High-contrast B-lenses compatible
Long-term brightness stability	40,000 hrs @ average usage conditions
Housing	integrated cooling design and patented sealed optical assembly
Dimensions (WxLxH)	Projector incl feet: 710 x 1070 x 547 mm/ 27,95 x 42,13 x 21,54 inches (710 x 1132x 547 mm/ 27,95 x 44.55x 21,54 inches with B-lensholder)
Weight	90kg / 198.5lbs
Power requirements	single phase or triple phase 200-240V 16A
Heat load (max. power)	4600 BTU/h
Exhaust airflow	300 CFM
Ambient temperature	40°C/104F Max.
Ambient humidity	85% RH max
Media server	Barco Alchemy ICMP-X and other media server brands** supported.
Power consumption	1.4kW (3W in Eco mode)
Noise Level	50dB(A) @1m and 25°C ambient temperature
3D systems	Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.
Safety requirements	Class 1 risk group 3
User interface	Touch Display and / or web-based
Lateral lens color on edge of image	With 2K lens: 2 pixels average* With 4K lens: 1.5 pixels average* (* depends on lens, zoom, ...)
Notes	**projector configuration with ICP-D; contact Barco service for the list of supported brands

Last updated: 15 Nov 2022

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.