



# OverView OVD4621

46" near-seamless LCD video wall for high-end applications



Barco's OverView OVD4621 is a high-performance, high brightness (700 cd/m<sup>2</sup> typical) 46" LCD-panel, dedicated for use in tiled video wall applications. With a narrow bezel of 3.5 mm (0.14"), excellent colors and contrast, and a wide viewing angle, the OverView OVD4621 takes the visual performance of LCD video walls in high-end control rooms to a new level. Boasting very high brightness levels, the OverView OVD4621 remains clearly readable whatever the room's lighting conditions.

Its best in class temperature sensor controlled heat management system, uses ultra low noise fans to ensure optimal cooling at all time, maximizing the backlight's lifetime. Additional innovations and low power consumption ensure this panel delivers maximal image quality at a minimal TCO.

### **Saving costs with automatic color and brightness calibration**

All the different screens in a tiled LCD video wall need to be perfectly balanced in terms of colors and brightness, so regular calibration is essential. As the first and only manufacturer, Barco now introduces its SenseX automatic color and brightness calibration system, that lets you calibrate the complete wall within minutes, without any external sensor or manual intervention.

Available as Instant VideoWall bundle

Barco also offers complete packages, containing four, six or eight OverView OVD4621 displays to create a 2x2, 3x2 or 4x2 video wall respectively, complete with wall mounts and cables. Optionally, you can bundle it with a controller, and software. In this way, you have your completely configured video wall solution in one package.

**PRODUCT SPECIFICATIONS****OVERVIEW OVD4621**

<b>Panel</b>	
LCD technology	SPVA
Resolution	Full HD (1920 x 1080)
Backlight	Direct LED
Aspect ratio	16:9
Pixel density	48 dpi
Refresh rate	60 Hz
Luminance	700 cd/m <sup>2</sup> (typ.)
Contrast	3500:1 (typ.)
Viewing angle	H 178°   V 178°
White point	10,000 K
Calibration	SenseX automatic color and brightness calibration
Backlight lifetime	60,000 h (typ)
MTBF	100,000 h (half brightness)
Cooling	Ultra low noise fans
Screen haze	40%
Operating temperature	0-40°C
Operational humidity	10-80% non-condensing
Dust filters	ISO 14644-1 ISO class 8
Storage temperature	-20°C-60°C
Storage humidity	5-95% non-condensing
<b>Dimensions</b>	
Dimensions	1021.6 mm x 576.2 mm x 98.2   40.2" x 22.7" x 3.9"
Active screen diagonal	46" (1168 mm)
Active screen area	1018.1 mm x 572.7 mm   40.1" x 22.6"
Weight	22.8 kg
Total bezel width (two adjacent displays)	3.5 mm   0.14"
<b>Connectivity</b>	
DVI	2 inputs
Remote control	External dongle with approx. 1m 3.5mm Stereo Male to IR Receiver
OPS Open Pluggable Specification	Yes
DisplayPort	1 input/output
Ethernet port	2
HDCP	Yes
HDMI	1 input
USB	1 input (USB 2.0)
<b>Power</b>	
AC input voltage	100-240 VAC, 50-60 Hz
Power consumption	Typ: 120 W Max: 210 W
Heat dissipation	Typ: 409 BTU/h Max: 717 BTU/h
EnergyStar	Full wall EnergyStar

Last updated: 08 Oct 2018

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.