

# CompactLink

Cost-effective solution for data transmission up to 100m in between a digitizer and a LED wall, or in between 2 LED walls.



For certain Rental & Staging applications there is a long distance between the LED display and the digitizer.

Compactlink is a cost-effective, optical-based solution for medium range data transmissions in applications up to 100m. CompactLink can be used in between the digitizer and the LED wall, but also in between multiple LED walls.

Two types of CompactLink are available: 50m or 100 m.

**PRODUCT SPECIFICATIONS****COMPACTLINK****Order Information**

R9853320 CompactLink 50  
R9853330 CompactLink 100  
R9853340 CompactLink cable interface kit

**Last updated: 26 Nov 2019**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.