

# Hemispherical lens (HR95) up to WQXGA



Focus range: 1.0 m - infinity

Field of view

- 1,920 x 1,080: 195° x 172° (1126 pixels)
- 1,920 x 1,200: 195° x 195° (1126 pixels)
- 1,400 x 1,050: 195° x 195° (889 pixels)
- 2,560 x 1,600: 195° x 179° (1609 pixels)

Order Only, MOQ 10pcs.

**PRODUCT SPECIFICATIONS****HEMISPHERICAL LENS (HR95) UP TO WQXGA**

---

Working F/#	F 3.0
Zoom ratio	No zoom
Focal length	4.08 mm
Focus Range	1m -infinity
Custom focus range	Extended focus range is available, please contact sales for details
Field of view (FOV)	<ul style="list-style-type: none"><li>■ 1,920 x 1,080 (projecting 1,200 x 1,080 pixels): 195° x 172° (1,126 pixels at 180°)</li><li>■ 1,920 x 1,200 (projecting 1,200 x 1,200 pixels): 195° x 195° (1,126 pixels at 180°)</li><li>■ 1,400 x 1,050 (projecting 947 x 947 pixels): 195° x 195° (889 pixels at 180°)</li><li>■ 2,560 x 1,600 (projecting 1,714 x 1,600 pixels): 195° x 179° (1,609 pixels at 180°)</li></ul>

---

**Last updated: 30 Nov 2021**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.