

CSC Base Unit

ClickShare wireless base station



Although not always visible, the Base Unit is the brain of the ClickShare system. This processing unit receives the wireless stream from the Buttons, and makes sure it is reproduced in the right way.

PRODUCT SPECIFICATIONS**CSC BASE UNIT**

| | |
|---------------------------|--|
| Weight | 2.6 kg/5.75 lb |
| Dimensions (HxWxD) | 181mm (incl. antennas) x 260mm x 276mm (Min.) / 7.125" (incl. antennas) x 10.236" x 10.9" (Min.) |
| Power input | 100-240 V 50-60 Hz 0.75-3 A |
| Power consumption | Shutdown: 2.5W Operation (typical): 20W Maximum: 35W |

Last updated: 29 Mar 2021

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.