

FLD+ 1.2 - 1.7 : 1 (EN43)

F35/F70/F90: 1.12 - 1.58 : 1 (WUXGA) / 1.2 - 1.7 : 1
(WQXGA/4K UHD) / F80: 1.68 - 2.38 : 1 (WQXGA/4K UHD)



Throw ratio

- SX+ 1.20-1.70:1
- 1080 / WUXGA 1.12-1.58:1
- Panorama / WQXGA 1.20-1.70:1
- F80: 1.68 - 2.38 : 1 (WQXGA/4K UHD)
(F80 requires the FLD/FLD+ lens adapter)

PRODUCT SPECIFICATIONS**FLD+ 1.2 - 1.7 : 1 (EN43)**

Working F/#	F 2.4-2.7 Motorized Iris F# 2.4-6.5
Zoom ratio	1.42 Motorized zoom and focus
Focal length	23.95-34.02 mm
Focus Range	1.5-15 m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.84 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ WQXGA 1.2-1.7:1■ 1080p /WUXGA 1.12-1.58 :1■ SXGA+ 1.2-1.7:1

Image size tolerance +/-2%

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.