

FLD+ 1.7 - 2.5 : 1 (EN41)

F35/F70/F90: 1.58 - 2.33 : 1 (WUXGA) / 1.7 - 2.5 : 1 (WQXGA/4K UHD) /F80:
2.38 - 3.51 : 1 (WQXGA/4K UHD) (F80 requires the FLD/FLD+ lens adapter)



Throw ratio

- SX+ 1.71-2.52:1
- 1080 / WUXGA 1.58-2.33:1
- Panorama / WQXGA 1.70-2.50:1
- F80: 2.38 - 3.51 : 1 (WQXGA/4K UHD)
(F80 requires the FLD/FLD+ lens adapter)

PRODUCT SPECIFICATIONS**FLD+ 1.7 - 2.5 : 1 (EN41)**

Working F/#	F 2.1-2.5 Motorized Iris F# 2.1-6.5
Zoom ratio	1.47 Motorized zoom and focus
Focal length	33.7-49.54 mm
Focus Range	Standard: 1.5m – 15m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	2.54 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ WQXGA 1.7-2.5 :1■ 1080p /WUXGA 1.58-2.33 :1■ SXGA+ 1.71-2.52:1

Image size tolerance +/-2%

Last updated: 13 Nov 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.