

# FLD+ 0.65 : 1 (EN47)



Focus range 0.5-4.0 m

Throw ratio

- SX+ 0.66:1
- 1080 / WUXGA 0.61:1
- Panorama / WQXGA 0.65:1
- F80: 0.91 : 1 (WQXGA/4K UHD)  
(F80 requires the FLD/FLD+ lens adapter and custom third part support is needed)

**PRODUCT SPECIFICATIONS****FLD+ 0.65 : 1 (EN47)**

---

Working F/#	F 2.1 Motorized Iris F# 2.1-6.0
Zoom ratio	No zoom Motorized focus
Focal length	12.6 mm
Focus Range	Optical Performance 0.5-4.0 m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	5.4 kg
Throw Ratio	DMD chip <ul style="list-style-type: none"><li>■ WQXGA 0.65:1</li><li>■ 1080p/WUXGA 0.65:1</li><li>■ SXGA+ 0.65:1</li></ul>

---

Image size tolerance +/-5%

Last updated: 24 Feb 2021

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.