


# FLD+ 0.65 : 1 (EN47)

F35/F70/F90: 0.61:1 (WUXGA) / 0.65:1 (WQXGA/4K UHD) /  
F80: 0.91 : 1 (WQXGA/4K UHD) (F80 requires the FLD/FLD+



Focus range 0.5-4.0 m

Throw ratio

- SX+ 0.66:1
- 1080 / WUXGA 0.61:1
- Panorama / WQXGA 0.65:1
- F80: 0.91 : 1 (WQXGA/4K UHD)  
(F80 requires the FLD/FLD+ lens adapter and custom third part support is needed)

**PRODUCT SPECIFICATIONS****FLD+ 0.65 : 1 (EN47)**

---

<b>Working F/#</b>	F 2.1 Motorized Iris F# 2.1-6.0
<b>Zoom ratio</b>	No zoom Motorized focus
<b>Focal length</b>	12.6 mm
<b>Focus Range</b>	Optical Performance 0.5-4.0 m
<b>Custom focus range</b>	Extended focus range is available, please contact sales for details
<b>Weight</b>	5.4 kg
<b>Throw Ratio</b>	DMD chip <ul style="list-style-type: none"><li>■ WQXGA 0.65:1</li><li>■ 1080p/WUXGA 0.65:1</li><li>■ SXGA+ 0.65:1</li></ul>

---

Image size tolerance +/-5%

**Last updated: 13 Nov 2018**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.