

FLD+ 2.5 - 4.6 (EN44)

F35/F70/F90: 2.33 - 4.3 : 1 (WUXGA) / 2.5 - 4.6 (WQXGA/4K UHD) F80: 3.51 – 6.45 : 1 (WQXGA/4K UHD) (F80 requires the FLD/FLD+ lens adapter)



Throw ratio

- SX+ 2.50-4.60:1
- 1080 / WUXGA 2.33-4.30:1
- Panorama / WQXGA 2.50-4.60:1
- F80: 3.51 – 6.45 : 1 (WQXGA/4K UHD) (F80 requires the FLD/FLD+ lens adapter)

PRODUCT SPECIFICATIONS**FLD+ 2.5 - 4.6 (EN44)**

Working F/#	F 2.1-2.93 Motorized Iris F# 2.1-6.5
Zoom ratio	1.85 Motorized zoom and focus
Focal length	49.52-91.6 mm
Focus Range	Optical Performance 2.5-25 m Mechanical 2.0-40 m
Custom focus range	Extended focus range is available, please contact sales for details
Weight	3.08 kg
Throw Ratio	DMD chip <ul style="list-style-type: none">■ WQXGA 2.50-4.60 :1■ 01080p /WUXGA 2.33-:4.3 : 1■ SXGA+ 2.5-4.60 :1
	Image size tolerance +/-2%

Last updated: 04 Jul 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.