

# FLD 3.8 - 6.5 : 1 (EN16)

4.1 - 7.1:1 (SX+) / 3.8 - 6.5 : 1 (WUXGA)



Focus range: 4.0 - 40.0 m

Throw ratio

- SX+ 4.10-7.10:1
- 1080 / WUXGA 3.80-6.50:1

**PRODUCT SPECIFICATIONS****FLD 3.8 - 6.5 : 1 (EN16)**

---

<b>Working F/#</b>	F 2.1-2.66 Motorized Iris F# 2.1-6.5
<b>Zoom ratio</b>	1.74 Motorized zoom and focus
<b>Focal length</b>	78.3-136.2 mm
<b>Focus Range</b>	Standard: 4m – 40m
<b>Custom focus range</b>	Extended focus range is available, please contact sales for details
<b>Weight</b>	2.5 kg
<b>Throw Ratio</b>	DMD chip <ul style="list-style-type: none"><li>■ 1080p /Wuxga 3.8-6.5:1</li><li>■ SXGA+ 4.1-7.1:1</li><li>■ 720p 4.5-7.8.1</li><li>■ XGA 5.6-9.7:1</li></ul>

---

Image size tolerance +/-5%

**Last updated: 13 Nov 2018**

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.