

# Galaxy 7 Classic+

SXGA+, 7 000 lumens three-chip DLP 3D stereo projector



**PRODUCT SPECIFICATIONS****GALAXY 7 CLASSIC+**

<b>Light output</b>	4650 ANSI lumens (Economy mode) 7000 ANSI lumens (Normal mode)		
<b>Resolution</b>	1400 x 1050 (SXGA+) native resolution		
<b>Brightness uniformity</b>	>90% for the total screen area		
<b>Contrast ratio</b>	1600:1 (full white/full black)		
<b>Lamp</b>	1.2 kW (Xenon illumination system) -800 W in Economy mode Typical / max. lifetime: 1200 / 1500 hours (Normal mode) 1700 / 2000 hours (Economy mode)		
<b>Features</b>	<p>Standard:</p> <ul style="list-style-type: none"> <li>• Bi-cubic WARP™</li> <li>• Synchronous and asynchronous active stereo display</li> <li>• DynaColor™/Linked DynaColor™</li> <li>• CLO (Constant Light Output)/ Linked CLO</li> <li>• Stereo-Creator</li> <li>• i-Blend™ (two-or three channel)</li> <li>• Economy mode</li> <li>• Shutter</li> </ul> <p>Optional:</p> <ul style="list-style-type: none"> <li>• Optical Soft Edge Matching (OSEM)</li> <li>• Infitec™ (Switchable)</li> <li>• External polarization (linear or circular)</li> <li>• GISCU™: multi-system and multi-site color management</li> </ul>		
<b>Noise Level</b>	< 60 dBA at 40°C < 54 dBA at 20°C		
<b>Compatibility</b>	<ul style="list-style-type: none"> <li>• Active stereo capabilities up to SXGA+ at 118Hz</li> <li>• WARP 6™ based pixel map processor using bi-cubic interpolation algorithms for advanced geometry corrections up to a pixelclock of 205 MHz</li> <li>• All current available video sources in RGB or DVI</li> </ul>		
<b>Inputs</b>	1 multifunctional 5-cable input (high bandwidth) for connection of: <ul style="list-style-type: none"> <li>• RGB analog signals with standard sync (BNC connectors), sync on green or separate sync</li> <li>• 1 Stereo sync input (mini DIN)</li> <li>• 2 stereo outputs (coax)</li> <li>• 1 DVI input</li> </ul>		
<b>Communication</b>	<ul style="list-style-type: none"> <li>• RS232 or RS422 loop-through input (D9-connector) for PC-based projector control</li> <li>• Communication input (D9 connector) for peripherals</li> </ul>		
<b>Lenses</b>	Lens type	order nr.	throw ratio
	Fixed lens (Manual focus)		
	TLD (0.8:1) HB*	9842040	0.75
	TLD+ (1.2:1)	9840775	1.23
	Motorized zoom and focus		
	TLD (1.6-2.0:1) HB*	9842060	1.5 to 1.8
	TLD (2.0-2.8:1) HB*	9842080	1.8 to 2.6
	TLD (2.8-5.0:1) HB*	9842100	2.6 to 4.6
	TLD (5.0-8.0:1) HB*	9842120	4.6 to 7.3
	* High brightness lens		
<b>Lens Shift</b>	Motorized V shift: up to 100% Motorized H shift: up to 65%		
<b>Power consumption</b>	Normal mode: 1700 Watts Economy mode: 1400 Watts		
<b>AC power</b>	230V (tolerance 180V -255V)		
<b>Ambient temperature</b>	Max. 35°C		
<b>Weight</b>	Net weight: 124 lbs/56 kg Shipping weight: 210 lbs/95 kg		

Last updated: 02 Mar 2021

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.