

F90-4K13

11,800 lumens, 4K UHD, DLP laser phosphor projector



- **Razor-sharp 4K images**
- **Ultimate installation flexibility, 24/7 operation**
- **Increased uptime, reduced costs**

The stunning image quality and laser phosphor light source of Barco's F90 projectors enable you to provide exceptional experiences while saving both time and money. Designed for installation in everything from high demanding visitor attractions to simulation applications that require 24/7 operation, the reliable F90 4K13 is equally suited for events, retail and advertising as well as boardrooms and auditoriums. Thanks to its 3D functionality, the projector is also perfectly fit for theme park dark rides and interactive experiences.

Superior image quality

The F90-4K13 delivers razor-sharp images at 4K UHD resolution with a high level of detail, and highly saturated colors that meet the Rec. 709 color space. Featuring an advanced optical design, this reliable projector provides a constant light output, for long-term, worry-free operation.

Unprecedented business value

The F90-4K13 projector enables you to increase uptime while driving costs down. Through its laser-phosphor light source and advanced cooling design, it provides up to 40,000 hours operating time without need for lamp changes - resulting in considerable cost-savings on maintenance and consumables.

Ultimate installation flexibility

This projector can run in any orientation, giving you more flexibility in projector location and orientation. Thanks to its wide array of high-resolution FLD and FLD+ lenses – from ultra-short throw (0.3:1) to long throw (9.75:1) – each providing a wide lens shift range, the F90-4K13 accommodates almost any projector configuration.

PRODUCT SPECIFICATIONS**F90-4K13**

| | |
|---|---|
| Projector type | Single chip DLP laser phosphor projector |
| Resolution | 3,840 x 2,400 (4K UHD) / 2,560 x 1,600 (WQXGA native) |
| Brightness | 11,800 center lumens |
| Contrast ratio | 1,800:1 sequential, 10,000:1 dynamic* |
| Brightness uniformity | 90% |
| Aspect ratio | 16:10 |
| Lens type | FLD+ |
| Optical lens shift | Vertical up to 146%, depending on lens Horizontal up to 70%, depending on lens Motorized zoom and focus (+ lens memory FLDX lenses) Motorized lens shift (with position memory on all lenses) |
| Color correction | P7 RealColor™ |
| CLO (constant light output) | Yes* |
| Light source | Laser phosphor |
| Light source lifetime | Up to 60,000 hours, depending on mode of operation |
| Sealed DLP™ core | Yes |
| Orientation | 360° rotation, no restrictions |
| 3D | Active stereoscopic 3D |
| Image processing | Embedded warp & blend engine |
| Keystone correction | Yes |
| Inputs | HDMI, 2x DP 1.2, 2x dual link DVI-D, HDBaseT, HDMI2.0 (HDCP2.2, HDR10), RJ 45 Ethernet, DMX in/out*, RS232 in, 2x USB, 12v out |
| Input resolutions | Up to 4K UHD @ 60Hz / Up to 2,560 x 1,600 @ 120Hz refresh rates: 24Hz to 120Hz for WQXGA (2560x1600) and 24Hz to 60Hz for 4K/4KUHD (4096 x 2160/ 3860 x 2400) |
| Software tools | Projector Toolset |
| Control | IR, RS232, RJ45, XLR wired |
| Network connection | 10/100 Ethernet, RJ45 |
| Power requirements | 100-240V / 50-60Hz |
| Power consumption | 1500 W nominal, 2180 W maximum |
| BTU per hour | 5100 BTU/h nominal, 7430 BTU/h maximum |
| Standby power | |
| Noise level (typical at 25°C/77°F) | 38 dB(A) |
| Operating temperature | 10 -45 °C (sea level) |
| Storage temperature | -20 to 60 °C |
| Operating humidity | 20 -80% RH |
| Storage humidity | 10 -90% RH |
| Dimensions (WxLxH) | 575 x 730 x 295 mm / 22.64 x 28.74 x 11.61 in |
| Weight | 44.5 kg / 98.1 lbs |
| Standard accessories | Power cord, wireless remote control |
| Certifications | CE, FCC Class A, cNemkoUS, CCC, EAC, KSA, KCC, RCM, UkrSEPRO |
| Warranty | Limited 3 years parts and labor. Extendable up to 5 years |
| 24-7 documentation | This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications. |
| Notes | * SW upgradable. Please contact an authorized Barco representative for details. ** When used in long-life mode, available through SW upgrade |

Last updated: 25 Jun 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.