


MiTRIX

Medium pitch, transparent, modular LED display with an ultra-wide viewing angle



IP65
WATERPROOF



PRODUCT SPECIFICATIONS**MITRIX**

Pixel pitch	24 mm
Tile pitch	384mm horizontal 192mm vertical
Brightness	3000 Nit
Pixel density	1736 LEDs / m ²
Pixel density	1736 LEDs / m ²
LED configuration	3-in-1 SMD
Hor. viewing angle	> 145°
Vert. viewing angle	> 145°
Transparency	55%
Lifetime	50.000 hours
Power consumption	50W / tile
Weight / Tile	1.3 kg
Processing	16-bit per color @ 50Hz
Colors	185 trillion
Refresh rate	800Hz minimum (PAL/NTSC)
Truss build-up	Max. 48 tiles high (9,2 m)
Operating temperature range	<ul style="list-style-type: none">■ 24 MiTRIX tiles per controller / typical video content: -20°C to +40°C ambient.■ 20 MiTRIX tiles per controller / full white content: -20° to +35°C■ 20 MiTRIX tiles per controller / typical video content: -20°C to +45°C
Tile dimensions	384 x 192mm
Tile dimensions	384 x 192mm
Tile dimensions	384 x 192mm
Tile dimensions	384 x 192mm
Operating humidity range	10 to 99%
D320 input compatibility	Data DVI up to UXGA, SDI, HD-SDI, S-video, composite, YUV
Certifications	ETL, CE, TUV, FCC class A
Order Information	R9004085B4 (Box of 4 tiles + link cable) R9004085F24 (Flightcase with 24 tiles + link cables) R9004087 (Controller -for up to 24 tiles) R9005086 (4 x hanging brackets)

Last updated: 26 Nov 2019

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.