


# DP2K-6E

Compact DLP Barco Alchemy Cinema projector for screens up to 7.5m (24ft) wide



- **Twice as quiet as the quietest digital cinema projector**
- **Simple UHP lamp swap for easy maintenance**
- **Fully integrated and DCI-compliant projector**

## **Taking digital cinema where it's never gone before**

The DP2K-6E brings compact, fully integrated and DCI compliant digital cinema projection to small and independent cinemas worldwide. And how!

## **Why you'll love the DP2K-6E**

- Cost-effective and fully integrated thanks to its on-board Barco Alchemy Series 3 module
- UHP lamps enable easy maintenance and compact design
- Twice as silent as the quietest projector currently on the market and super compact
- Trademark Barco quality, and modularity, now also for the smallest screens

Series 3 electronics combining media server functionality with cinema processing electronics

Fewer boxes lead to higher reliability and ease-of-use

Simple operation thanks to the intuitive 'Barco Web Commander' user interface

- Series 3 electronics combining media server functionality with cinema processing electronics
- Fewer boxes lead to higher reliability and ease-of-use
- Simple operation thanks to the intuitive 'Barco Web Commander' user interface

**PRODUCT SPECIFICATIONS****DP2K-6E**

<b>Native resolution</b>	2,048 x 1,080 pixels
<b>Housing</b>	Hermetically sealed DMDs and optical assembly
<b>Light output</b>	DCI colors: 4,800 lumens / Non-DCI: 7,200 lumens
<b>Lamps</b>	Dual 465W, UHP lamps
<b>Screen size</b>	Up to 7.5m/24.6 ft wide (screen gain 1.2 @ 14ft)
<b>Contrast ratio</b>	1,600:1
<b>Digital MicroMirror Device™</b>	3 x 0.69" DC2K dark metal devices
<b>Prime lenses</b>	Fully motorized 1.2 -1.7 1.34 -1.9 1.5 -2.15 1.7 -2.55 2.0 -3.9
<b>Control I/O</b>	3x Ethernet (RJ 45) 8x GPIO (DB 25) 3D interface USB interface
<b>Integrated Cinema Media Processor</b>	DCI 4K 2D up to 60fps DCI 4K 3D (24 or 30 fps per eye) DCI High Frame Rates 2K 3D up to 120fps (60fps per eye) JPEG 2000 bit-rates up to 625Mbps Dual-channel color-correction MPEG-2 (4:2:0 and 4:2:2 up to 60fps) 2x HDMI2.0a (up to 4K 2D 60fps) 2x 3G-SDI inputs 16x AES/EBU audio channels (2x RJ45) 8x GPI, 8x GPO (4x RJ45) 2x Gbe for content connectivity & ingest 2x front-accessible USB 3.0 for fast ingest 2x front-accessible USB 2.0 Video watermarking: Civolution NexGuard Audio watermarking: Civolution Closed captioning devices: Support for SMPTE 430-10
<b>Integrated storage</b>	1.9TB effective storage (RAID-5) / 3x 1TB Hot-swappable 2.5" hard-drives 3.9TB effective storage (RAID-5) / 3x 2TB Hot-swappable 2.5" hard-drives
<b>Barco Web Commander</b>	Projector Dashboard Projector Control Board Show Player/Editor/Scheduler Automation, 3D, Ingest TMS integration Smart Projector Status Via HTML5 web-browsers including iOS & Android tablets
<b>Barco Communicator</b>	Projector installation & configuration Projector update & maintenance
<b>Power requirements</b>	200-240 VAC
<b>Projector dimensions (HxWxD)</b>	369 x 689 x 664 mm 14.5 x 27.1 x 26.1 inch
<b>Projector weight</b>	53.8 kg / 119 lbs (including recessed handles for easy carrying)
<b>Ambient temperature</b>	35°C / 95°F Max.
<b>Options</b>	Barco CineMate App (iOS & Android) -free 3D add-ons Touch screen monitor, inc. Barco Commander & Communicator Pedestal CineCare Web Auro 11.1 license Barco Escape license Live 3D*** Ceiling mount kit*** (***) roadmap)
<b>Noise Level</b>	48 dB(A)
<b>Airflow requirements</b>	43 CFM

Last updated: 24 Feb 2021

Technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest information.