

BlendPRO-II

BlendPRO-II adds widescreen blending capability to the ScreenPRO-II family.



PRODUCT SPECIFICATIONS**BLENDPRO-II**

| | |
|----------------------|--|
| Video Input | Input Types: Four (4) Digital DVI channels per DDWG 1.0 on DVI-I connector Resolution: VGA up to UXGA @60 Hz (including all progressive HD resolutions and 1920x1200 and 2048x1080) |
| Video Output | Four (4) high resolution channels Digital DVI channels per DDWG 1.0 on DVI-I connectors and Analog RGBHV on HD-15 connectors |
| User Control | Controlled from ScreenPRO-II controller via Ethernet |
| Physical | 2 RU Rackmount Chassis |
| Input power | 100-240 VAC, 50-60 Hz, 175 W max. |
| Environmental | Temperature: 0-40 degrees C; Humidity: 0-95% non-condensing |

Last updated: 27 Aug 2018

Technical specifications are subject to change without prior notice. Please check www.barco.com for the latest information.